

ATTENTION: POUR TOUTE INTERVENTION SUR L'APPLIQUE, COUPER L'ALIMENTATION.

CAREFUL: FOR THIS OPERATION YOU HAVE TO CUT OFF THE POWER.

ACHTUNG: FÜR DIESE HAND HABUNG MÜSSEN DER STROM UNTERBROCHEN.

CUIDADO: PARA CUALQUIER INTERVENCION EN EL APPLIQUE, CORTAR LA ALIMENTACION ELECTRICA.

ATTENZIONE: PER QUELUNQUE INTERVENTO SULL'APPLIQUE INTERRUPELLE L'ALIMENTAZIONE ELETTRICA.

ATELIER SEDAP
LES BEAUX ARTS DU PLÂTRE

Tension: 230/240 Volts
Fréquence: 50 Hertz

018020418-0

Luminaire Classe 2	Classe 2 lamp	Leuchten Klasse 2	Luminario de clase 2	Lume Classe 2
Type de lampe: Halogène GU10 4 x 50W / GU10	Bulb type: Halogen GU10 4 x 50W / GU10	Glasbime typ: Halogen GU10 4 x 50W / GU10	Lipo de bombilla: Halogena GU10 4 x 50W / GU10	Typo di ampola: Alogena GU10 4 x 50W / GU10

MAXIMUM 4 x 50W
GU10

